

## Garant

### Jobber drill extra long HSS FS, uncoated, Ø DC h8 × overall length L: 7X290mm



#### Order data

Order number	116240 7X290
GTIN	4045197028822
Item class	11B

#### Description

##### Version:

With precision ground point.

Significantly strengthened core without core taper. Bright finish flutes, nitrided chamfers.

With point geometry shape C.

##### Advantage:

**Special deep hole drills. For particularly deep or recessed holes.** Good chip evacuation due to parabolic flutes, resulting in fewer chip evacuations even in particularly deep holes.

##### Recommendation:

##### Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c.$$

##### Note:

Suitable NC spotting drills No. 112120, 112140 and 112170 with **142° tip angle** for enhanced process reliability

#### Technical description

Feed f in steel < 750 N/mm <sup>2</sup>	0.07 mm/rev.
Nominal Ø D <sub>c</sub>	7 mm
Flute length L <sub>c</sub>	200 mm
Number of cutting edges Z	2
Tolerance nominal Ø	h8
Shank Ø D <sub>s</sub>	7 mm
Overall length L	290 mm

Standard	DIN 1869
recommended maximum drilling depth L <sub>2</sub>	189.5 mm
Point angle	130 degrees
Shank	Plain shank
Coating	uncoated
Tool material	HSS
Type	FS
Helix angle	38 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable only under restricted conditions	50 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	32 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	28 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	21 m/min	P
GG(G)	suitable	18 m/min	K
Oil	suitable		
wet maximum	suitable		