



## Mechanic's pin punches, Point Ø D: 3 mm



### Order data

Order number	747500 3
GTIN	7610733200481
Item class	73B

### Description

#### Version:

Round steel, exceptionally slim and handy. With knurled shank. Through hardened, **head specially annealed** to prevent splintering. Highest possible tip hardness (approx. 59 HRC) with exceptional toughness. Actual Ø 0.05 - 0.5 mm less than nominal Ø, prevents the pin punch jamming in the hole.

#### Material:

Extra chrome vanadium steel, surface chrome-plated.

overall length L<sub>1</sub>: 110 mm

Mandrel length L<sub>2</sub>: 25 mm

Shank Ø S: 7 mm

### Technical description

overall length L <sub>1</sub>	110 mm
Mandrel length L <sub>2</sub>	25 mm
Shank Ø S	7 mm
Point Ø D	3 mm
Point hardness	59 HRC
Type of striking head	head specially annealed
Material	Extra chrome vanadium steel
Surface	chrome-plated

