



## Pin punch, special quality chrome-plated, Point Ø D: 16mm



### Order data

Order number	746900 16
GTIN	7610733024148
Item class	73B

### Description

#### Version:

Sturdy octagonal shank with cylindrical shaft. Uniformly through hardened over the entire length. **Head specially annealed** to prevent splintering. Actual Ø 0.05 - 0.5 mm less than nominal diameter, prevents the pin punch from jamming in the hole.

**Special quality**, i.e. highest possible tip hardness – approx. 59 HRC – with exceptional toughness.

#### Material:

Special quality of extra chrome vanadium steel, chrome-plated.

### Technical description

Point Ø D	16 mm
overall length L <sub>1</sub>	260 mm
Shank Ø S	18 mm
Mandrel length L <sub>2</sub>	130 mm
Point hardness	59 HRC
Material	Special quality of extra chrome vanadium steel
Surface	chrome-plated
Type of product	Parallel pin punches

