



Multi-function heavy-duty side cutter VDE insulated, overall length: 180mm



Order data

Order number	728790 180
GTIN	4007582006488
Item class	76B

Description

Version:

Induction hardened precision cutting edges (approx. 64 HRC) for piano wire. Precision stripping knife for single-core (solid) conductors 1.5 and 2.5 mm². Precise crimping profile for 1.5 and 2.5 mm² terminal sleeves. Shearing cutter for cutting M3.5 and M4 brass and copper screws to length with a flat cut. Bending device for forming solid copper wires Ø 4, 5, and 6 mm into eyes. Handles with thick-walled grips **insulated up to 1000V according to DIN EN ICE 60900 / VDE 0682-201**. High cutting and crimping power due to optimum leverage.

Application:

Ideal for electrical installation work - offset design for improved ergonomics and a clear view of the working area.

Material:

Special tool steel, jaws bright finished, handles with multi-component covering.

Technical description

overall length	180 mm
Cutting capacity piano wire Ø	2 mm
Wire stripping for conductor Ø	1.5 mm
Wire stripping for conductor Ø	2.5 mm
for terminal sleeves	1.5 mm ²
for terminal sleeves	2.5 mm ²
Weight	270 g

angled head	25 degrees
Standard	DIN EN IEC 60900 / VDE 0682-201
Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Material	Special tool steel
Surface of pliers	bright finish
Type of product	Cutting pliers