

Garant**Assembly trolley, Type: TB3/0****Order data**

Order number	918583 TB3/0
GTIN	4045197684158
Item class	91T

Description**Version:**

Sturdy welded tubular steel frame. For modular mounting of carrier rails for open storage bins. Can be used on both sides, 8 carrier rails can be inserted per side (allow for the access height of the bins). Carrier rails can be inserted at intervals of 50 mm and have a load capacity of 30 kg. Ergonomic 2-component Haptoprene® push handle. 2 fixed wheels and 2 castors (with parking brake) with treadless polyurethane tyres and roller bearings.

Supplied with:

empty.

Colour:

Silver **powder-coated.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Width	1225 mm
Usable depth	700 mm

Usable width	1000 mm
Weight	27.2 kg
maximum load capacity	250 kg
Height	1200 mm
Number of castors with parking brake	2
Suspension interval	50 mm
Usable height	900 mm
Depth	710 mm
Type	TB3/0
Number of fixed wheels without parking brake	2
Wheel Ø	125 mm
Height adjustment interval	50 mm
Type of product	Materials supply trolley