

LOCTITE**Nut lock, 250 ml, Manufacturer ID: 2701_EPIG****Order data**

Order number	083303 2701_EPIG
GTIN	8000776157948
Item class	04L

Description**Version:****Thread locking fluid.**

One-part anaerobic adhesives for all types and forms of thread. Screwed joints are gas-tight, oil-tight and watertight. Seizing is reliably prevented.

Application:

Low strength – can be undone with normal tools.

Medium strength – can still be undone with normal tools.

High strength – Can be undone only with special tools or by heating (>150 °C). Ideal for use on passive surfaces such as high-alloy CrNi steels.

Note:

Before applying locking fluid, clean the threads with general-purpose cleaner No. 083391 / 3392.

Quick and easy handling for 50 ml bottles with No.083344 size50.

Labelling of hazardous substances: GHS07 Caution

Manufacturer's designation: 2701

Colour of thread locking: green

minimum break-away torque: 38 N·m

Temperature range: -55 - 150 °C

for thread size M to: M20

Functional strength: 6 h

Technical description

Top-up fluid	250 ml
Content of stick	g
Product name attribute	250 ml
Type of product	

