

Garant**Assembly trolley, Type: TB3/G96****Order data**

Order number	918583 TB3/G96
GTIN	4045197693914
Item class	91T

Description**Version:**

Sturdy welded tubular steel frame. For modular mounting of carrier rails for open storage bins. Can be used on both sides, 8 carrier rails can be inserted per side (allow for the access height of the bins). Carrier rails can be inserted at intervals of 50 mm and have a load capacity of 30 kg. Ergonomic 2-component Haptoprene® push handle. 2 fixed wheels and 2 castors (with parking brake) with treadless polyurethane tyres and roller bearings.

Supplied with:

Fitted with 12× carrier rails No. 918584 size TB3, 48× GARANT open storage bins No. 963301 size AA1 and 48× GARANT open storage bins No. 963301 size AB1.

Colour:

Silver **powder-coated.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Type	TB3/G96
Width	1225 mm

Number of castors with parking brake	2
Number of open storage bins	96
Usable height	900 mm
maximum load capacity	250 kg
Height	1200 mm
Usable width	1000 mm
Suspension interval	50 mm
Depth	710 mm
Weight	27.2 kg
Usable depth	700 mm
Number of fixed wheels without parking brake	2
Wheel Ø	125 mm
Height adjustment interval	50 mm
Type of product	Materials supply trolley

Accessories

Push handle Colour BLUE	920135 BLUE
Open storage bin Type AB1	963301 AB1
Carrier rail for assembly trolley suitable for type TB3	918584 TB3
Push handle Colour BLACK	920135 BLACK
Open storage bin Type AA1	963301 AA1
Assembly trolley Type TB3/0	918583 TB3/0