

LOCTITE**Thread locking, 50 ml, Manufacturer's designation: 2701_EGFD**

Order data

Order number	083301 2701_EGFD
GTIN	2050001948823
Item class	04L

Description

Version:

The use of thread-lockers prevents the screw fastenings from accidentally releasing and coming undone. The single-component anaerobic adhesives are suitable for all thread types and forms. Screw fastenings are sealed. Seizing is reliably prevented.

Thread locking fluid.

Application:

Low strength – can be undone with normal tools.

Medium strength – can still be undone with normal tools.

High strength – Can be undone only with special tools or by heating (>150 °C). Ideal for use on passive surfaces such as high-alloy CrNi steels.

Note:

Before applying locking fluid, clean the threads with general-purpose cleaner No. 083391 and No. 083392. Quick and easy handling for 50 ml bottles with No. 083344 size 50.

Technical description

Manufacturer's designation	LOCTITE 2701
minimum break-away torque	38 Nm

Labelling of hazardous substances	GHS07: Exclamation mark
for thread size M to	M20
Chemical basis	Dimethacrylate ester
Storage temperature	8 - 21 °C
Operating temperature range	-55 - 150 °C
Suitable for application area	Thread locking
Suitable for application area	Joint connection
Suitable for application area	galvanised surfaces
Shape	liquid
Suitable for material	Metal
Working life after date of manufacture	17 mo
Flashpoint	93 °C
Colour	green
Capacity	50 ml
Characteristics	Can be released with normal tools
Characteristics	vibration-resistant
Characteristics	sealing
Characteristics	fluorescent under UV light
Characteristics	oil-tolerant
Functional strength to	6 h
Touch dry after	10 min
Dynamic viscosity	500 - 900 mPas
Disassembly	heavy-duty
Strength class	high-strength
Density	1.1 g/cm ³
Product name attribute	50 ml
Type of product	Thread lock

