

HOLEX
HOLEX Pro INOX solid carbide torus cutter HPC DIN 6535 HB, AlCrN, Ø DC / R1: 16/2,0mm

Order data

Order number	GG1248 16/2,0
GTIN	4045197908988
Item class	GGN

Description
Version:

Dimensions similar to DIN 6527.

For **outstanding tool life**.

For use at **high cutting speeds, particularly suitable even for steels up to approx. 1100N/mm²**.

Same as No. 206348.

Technical description

Feed f_z for side milling in INOX > 900 N/mm ²	0.072 mm
Flute length L_c	36 mm
Feed f_z for copy milling in stainless steel > 900 N/mm ²	0.088 mm
Shank Ø D_s	16 mm
No. of teeth Z	4
Shank	DIN 6535 HB to h6
Recess Ø D_1	15.5 mm

Overall length L	92 mm
Corner radius R ₁	2 mm
Overhang length L ₁ incl. recess	42 mm
Cutting edge Ø D _c	16 mm
Helix angle	35 degrees
Contents	5
Series	Pro Inox
Coating	AlCrN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Tolerance nominal Ø	f8
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Direction of infeed	horizontal, oblique and vertical
Cutting width a _e for milling operation	0.05×D for copy milling
Cutting width a _e for milling operation	0.3×D for side milling
Machining strategy	HPC
Shank tolerance	h6
Type of product	Torus cutter

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable	240 m/min	P
Steel < 750 N/mm ²	suitable	220 m/min	P
Steel < 900 N/mm ²	suitable	180 m/min	P
Steel < 1100 N/mm ²	suitable	180 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	150 m/min	P

TOOLOX 33	suitable only under restricted conditions	115 m/min	H
TOOLOX 44	suitable only under restricted conditions	80 m/min	H
INOX < 900 N/mm ²	suitable	100 m/min	M
INOX > 900 N/mm ²	suitable	85 m/min	M
Uni	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	suitable only under restricted conditions		

Accessories

HOLEX Pro INOX solid carbide torus cutterHPC DIN 6535
HB Ø DC / R1 16/2,0 mm

206348 16/2,0