



## HOLEX Pro INOX solid carbide torus cutter HPC DIN 6535 HB, AlCrN, Ø DC / R1: 20/2,0mm



### Order data

Order number	GG1248 20/2,0
GTIN	4045197909039
Item class	GGN

### Description

#### Version:

Dimensions similar to DIN 6527.

For **outstanding tool life**.

For use at **high cutting speeds, particularly suitable even for steels up to approx. 1100N/mm<sup>2</sup>**.

**Same as No. 206348.**

### Technical description

Corner radius R <sub>1</sub>	2 mm
No. of teeth Z	4
Feed f <sub>z</sub> for copy milling in stainless steel > 900 N/mm <sup>2</sup>	0.105 mm
Flute length L <sub>c</sub>	41 mm
Shank	DIN 6535 HB to h6
Feed f <sub>z</sub> for side milling in INOX > 900 N/mm <sup>2</sup>	0.085 mm
Overall length L	104 mm

Cutting edge $\varnothing D_c$	20 mm
Recess $\varnothing D_1$	19.5 mm
Shank $\varnothing D_s$	20 mm
Overhang length $L_1$ incl. recess	52 mm
Helix angle	35 degrees
Contents	5
Series	Pro Inox
Coating	AlCrN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Tolerance nominal $\varnothing$	f8
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Direction of infeed	horizontal, oblique and vertical
Cutting width $a_e$ for milling operation	0.05×D for copy milling
Cutting width $a_e$ for milling operation	0.3×D for side milling
Machining strategy	HPC
Shank tolerance	h6
Type of product	Torus cutter

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	240 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	220 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	150 m/min	P

TOOLOX 33	suitable only under restricted conditions	115 m/min	H
TOOLOX 44	suitable only under restricted conditions	80 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable	100 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	85 m/min	M
Uni	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	suitable only under restricted conditions		

## Accessories

HOLEX Pro INOX solid carbide torus cutterHPC DIN 6535  
HB Ø DC / R1 20/2,0 mm

206348 20/2,0