

Garant**Solid carbide milling cutter, AlCrN, Ø e8 DC: 14mm****Order data**

Order number	GG1294 14
GTIN	4045197907806
Item class	GGN

Description**Version:**

Dimensions similar to **DIN 6527**. Improved coating for general-purpose applications in steel and cast iron.

Same as No. 202294.

Technical description

Flute length L_c	26 mm
Shank	DIN 6535 HB to h6
Shank form	HB
Shank $\varnothing D_s$	14 mm
No. of teeth Z	3
Overhang length L_1 incl. recess	38 mm
Recess $\varnothing D_1$	13.8 mm
Tolerance nominal \varnothing	e8
Cutting edge $\varnothing D_c$	14 mm

Feed f_z for slot milling in steel < 750 N/mm ²	0.07 mm
Overall length L	83 mm
Corner chamfer width at 45°	0.3 mm
Direction of infeed	horizontal, oblique and vertical
Feed f_z for side milling in steel < 750 N/mm ²	0.1 mm
Helix angle	45 degrees
Corner chamfer angle	45 degrees
Contents	5
Coating	AlCrN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Cutting width a_e for milling operation	0.5×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	280 m/min	N
Alu > 10% Si	suitable only under restricted conditions	200 m/min	N
Steel < 500 N/mm ²	suitable	120 m/min	P
Steel < 750 N/mm ²	suitable	110 m/min	P
Steel < 900 N/mm ²	suitable	100 m/min	P
Steel < 1100 N/mm ²	suitable	70 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	60 m/min	P
INOX < 900 N/mm ²	suitable	70 m/min	M

INOX > 900 N/mm ²	suitable only under restricted conditions	50 m/min	M
GG(G)	suitable	90 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		
dry	Suitable only under restricted conditions		
Air	suitable		

Accessories

Solid carbide milling cutter Ø e8 DC 14 mm

202294 14