


Garant
Solid carbide milling cutter, AlCrN, Ø e8 DC: 20 mm

Order data

Order number	201307 20
GTIN	4045197930286
Item class	11X

Description
Version:

Dimensions similar to **DIN 6527**.

Improved coating for general-purpose applications in steel and cast iron.

Through-coolant: no

Tolerance nominal Ø: e8

No. of teeth Z: 2

Helix angle: 30 degrees

Direction of infeed: horizontal, oblique and vertical

Shank: DIN 6535 HE to h6

No. of teeth Z: 2

Flute length L_c : 38 mm

Overhang length L_1 incl. recess: 54 mm

Recess Ø D_1 : 19.7 mm

Overall length L: 104 mm

Shank Ø D_s : 20 mm

Technical description

No. of teeth Z	2
Corner chamfer width at 45°	0.1 mm
Overhang length L_1 incl. recess	54 mm
Shank Ø D_s	20 mm
Direction of infeed	horizontal, oblique and vertical
Overall length L	104 mm

Shank	DIN 6535 HE to h6
Feed f_z for side milling in steel < 750 N/mm ²	0.15 mm
Shank form	HB
Flute length L_c	38 mm
Feed f_z for slot milling in steel < 750 N/mm ²	0.1 mm
Recess $\varnothing D_1$	19.7 mm
Cutting edge $\varnothing D_c$	20 mm
Tolerance nominal \varnothing	e8
Helix angle	30 degrees
Corner chamfer angle	45 degrees
Coating	AlCrN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	$0.3 \times D$ for side milling
Through-coolant	no
Colour ring	without
Type of product	End mill