

Garant
Solid carbide milling cutter, AlCrN, Ø e8 DC: 11 mm

Order data

Order number	202269 11
GTIN	4045197930941
Item class	11X

Description
Version:

Dimensions similar to **DIN 6527**.

Improved coating for general-purpose applications in steel and cast iron.

Through-coolant: no

Tolerance nominal Ø: e8

No. of teeth Z: 3

Helix angle: 30 degrees

Direction of infeed: horizontal, oblique and vertical

Shank: DIN 6535 HB to h6

No. of teeth Z: 3

Flute length L_c : 26 mm

Overhang length L_1 incl. recess: 38 mm

Recess Ø D_1 : 10.8 mm

Overall length L: 83 mm

Shank Ø D_s : 12 mm

Technical description

Tolerance nominal Ø	e8
Direction of infeed	horizontal, oblique and vertical
Helix angle	30 degrees
No. of teeth Z	3
Overall length L	83 mm
Cutting edge Ø D_c	11 mm

Shank	DIN 6535 HB to h6
Corner chamfer width at 45°	0.3 mm
Shank form	HB
Feed f_z for side milling in steel < 750 N/mm ²	0.09 mm
Shank $\varnothing D_s$	12 mm
Flute length L_c	26 mm
Feed f_z for slot milling in steel < 750 N/mm ²	0.06 mm
Overhang length L_1 incl. recess	38 mm
Recess $\varnothing D_1$	10.8 mm
Corner chamfer angle	45 degrees
Coating	AlCrN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Cutting width a_e for milling operation	0.3×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Colour ring	without
Type of product	End mill