



Electronic torque analyser „TruCheck™ Plus“, maximum torque: 350N·m



Order data

Order number	654475 350
GTIN	2050001017604
Item class	66D

Description

Version:

- **3 user modes: Tracking display (Track), Trigger point sensing (First Peak), Peak value display (Final-Peak).**
- **Easy input of target torque with tolerances.**
- **Units of measure: Nm, lbfft, lbfin.**

Large easy to read LCD display. Data transmission can be performed by an RS232C connecting cable.

Advantage:

3 LEDs for quick and easy visual indication of status.

Supplied with:

RS232C connection cable to PC / printer or network mode and mains adapter, in sturdy plastic case.

Technical description

maximum torque	350 Nm
Display unit height	145.5 mm
Weight	2.5 kg
Display unit depth	85 mm
Square socket	1/2 in

Measuring range	10 - 350 Nm
Display unit width	150 mm
Torque measuring accuracy	±1 %
Power supply	Mains operated
Direction of tightening	For right and left-hand tightening
Interface	RS232C interface
Test certificate	Manufacturer's test certificate
Calibration	O4

Services

Calibration clockwise / anti-clockwiseTorque analyser / sensor maximum torque 400/2 N·m	020140 400/2
--	--------------

Accessories

RS232 PC connection cable	654344
---------------------------	--------