

## Garant

**“TWdrive” electronic torque/rotational angle wrench with plug-in ratchet, maximum torque: 15N·m**



### Order data

Order number	655255 15
GTIN	4045197683717
Item class	61E

### Description

#### Version:

Highly precise electronic torque / rotational angle wrench for very reliable screw tightening and checking of screw fastenings. Clear OLED display with colour screen and extremely simple menu navigation. Sturdy wrench with compact housing and sturdy rectangular section shaft. “Direct mode” allows quick general-purpose use. There are up to 200 user-specific screw tightening cases which can be programmed, which can be incorporated in procedural plans. 4 measurement modes: Torque and angle of rotation. Process reliability results achieved by torque with angular monitoring or rotational angle with torque monitoring. Memory capacity for up to 2500 measurements included. Can be programmed by a PC; password protection for security against tampering. Rotary angle measurement can be programmed easily, no reference arm required. Target values and tolerances can be specified. Peak and Track function modes. Integrated automatic reminder of calibration after the number of operations and elapsed time. Torque/rotational angle wrench with **outstanding ergonomics and uniquely user-friendly operation.**

**Units of measure:** Nm, lbfft, lbfin.

- **Reversible ratchet with ejector.**
- **Easy input of pitch settings: For tools with a different pitch setting simply input the new pitch. No laborious calculations with formulae.**
- **QuickRelease: Secure engagement and quick change of plug-in heads.**
- **Data output: The USB interface allows the saved data to be read out and analysed via PC.**
- **Warning signals: – Acoustic (buzzer) – Visual via 3 LEDs and a colour screen – Tactile (vibration in the handle)**
- **Secure controls. No double assignment of keys.**
- **Comfort setting**

Accuracy class  $\pm 3\%$ .

#### Standard:

Geprüft nach DIN EN ISO 6789.

**Supplied with:**

With sturdy plastic case (size 400 in a sturdy sheet metal case) and 3 batteries (1.5 V Mignon / AA / LR6), USB data cable, and software for transmitting the measured data.

Direction of tightening: For right- and left-hand tightening

Torque measuring accuracy:  $\pm 3\%$

Measuring accuracy rotational angle:  $\pm 2\%$

Exchangeable tool: Plug-in head

Interface: USB interface

Test certificate: Manufacturer's test certificate

Torque range: 1.5 - 15 N·m

Resolution: 0.01 N·m

Adjusted reference dimension on the torque wrench [ $l_2$ ]: 21 mm

Square drive: 1/4 in

Socket for plug-in head: 9×12 mm

**Technical description**

Socket for plug-in head	9×12 mm
maximum torque	15 N·m
Square drive	1/4 in
Resolution	0.01 N·m
Torque measuring accuracy	$\pm 3\%$
Exchangeable tool	Plug-in head
Torque range	1.5 - 15 N·m
Article no of the battery / rechargeable battery fitted	081557 LR6
Number of batteries contained	3
Series	TWdrive
Adjustable trigger value	adjustable
Connection format	for plug-in heads (rectangular socket)
Display	digital
Reversible reading	Nm
Reversible reading	lbf·in
Reversible reading	lbf·ft
Standard	DIN EN ISO 6789
Measurement process	Torque

Measurement process	Rotation angle
Lever length including factory calibration reference dimension [I <sub>3</sub> ]	262 mm
Adjusted reference dimension on the torque wrench [I <sub>2</sub> ]	21 mm
Trigger principle	Vibration motor
Setting the trigger value	digital, adjustable
Lever length without plug-in head [I <sub>1</sub> ]	242.5 mm
Feedback	displaying
Calibration	O3
Calibration	O5
Direction of tightening	For right- and left-hand tightening
Test certificate	Manufacturer's test certificate
Interface	USB interface
Measuring accuracy rotational angle	±2 %
Data can be recorded	yes
Measurement technology	electronic
Release signalling	optisk
Release signalling	akustisk
Release signalling	haptisk
Power supply	Battery-powered
Type of product	Torque Wrench

## Services

Labellinglaser-etched Type	018940
CalibrationTorque wrench both ends maximum torque 400/2 N·m	020030 400/2
CalibrationRotation angle Type W	020070 W
DAkkS calibrationTorque wrench both ends maximum torque 1000/2 N·m	020040 1000/2

## Accessories

Alkaline manganese battery set International size LR6	081558 LR6
Plug-in ratchetwith ejector Type-Square drive 1-1/2 in	657580 1-1/2
Plug-in ratchet reversiblewith ejector Type-Square drive 1-3/8 in	657582 1-3/8
Plug-in ratchet Type-Square drive 1-3/8 in	657630 1-3/8
Alkaline-manganese batteries International size LR6	081561 LR6
Plug-in ratchet reversiblewith ejector Type-Square drive 1-1/4 in	657582 1-1/4
Plug-in ratchet reversiblewith ejector Type-Square drive 1-1/2 in	657582 1-1/2
Plug-in ratchet Type-Square drive 1-1/4 in	657630 1-1/4
Plug-in ratchet Type-Square drive 1-1/2 in	657630 1-1/2
Plug-in ratchetwith ejector Type-Square drive 1-1/4 in	657580 1-1/4
Plug-in ratchet Square drive 1-3/8 in	657620 1-3/8
Alkaline-manganese batteries International size LR6	081551 LR6
"TWdrive" electronic torque/rotational angle wrenchwithout plug-in head maximum torque 15 N·m	655250 15