



## Short drill chuck Form A, SK 40, Clamping range: 2,5-16mm



### Order data

Order number	302565 2,5-16
GTIN	4045197931832
Item class	32K

### Description

**Version:**

For clockwise and anticlockwise rotation. Internal thread for manual clamping.

**Application:**

For clamping drills, countersinks, and reamers on milling machines.

**Supplied with:**

Supplied with Torx® chuck key with T-handle, for optimum clamping force.

### Technical description

Overhang dimension A	85 mm
External Ø D	56 mm
Clamping range	2.5 - 16 mm
Spare chuck key	SW6
Adapter	SK 40
Arbor standard	DIN 2080
Shape	A
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 50 µm
maximum tightening torque $M_{d\max}$	≤ 14 Nm
Type of product	Short drill chuck

