

**Garant****Short drill chuck Form A, HSK-A 63, Clamping range: 1-16mm****Order data**

Order number	307725 1-16
GTIN	4045197931887
Item class	31B

**Description****Version:**

- **For clockwise and anticlockwise rotation.**
- **With RFID/Balluffchip bore.**

With through coolant feed up to max. 50 bar.

Concentricity  $\leq 20 \mu\text{m}$ .

- **Slim design.**
- **Specific coolant transfer to tools with IC.**
- **Optimum holding torques at the tool.**

**Supplied with:**

**Clamping wrench** with T-handle.

**Optional extras:**

Socket wrench No. 309890. Coolant tube No. 309880.

**Technical description**

Clamping range	1 - 16 mm
External $\varnothing$ D	50 mm
Type	slim
Overhang dimension A	104 mm
Spare Torx® chuck key No. 625220	TX25
Adapter	HSK-A 63

Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-7
Arbor standard	DIN 69893-1
Shape	A
Through-coolant	yes, with max. 50 bar
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 20 µm
maximum tightening torque $M_{d\max}$	≤ 14 Nm
Type of product	Short drill chuck