

Garant**Short drill chuck, PSC 63, Clamping range: 1-16mm****Order data**

Order number	308595 1-16
GTIN	4045197932020
Item class	31B

Description**Version:**

- For clockwise and anticlockwise rotation.
- Sand-blasted.
- With RFID/Balluffchip bore.
- All shanks hard turned (for smooth running!).
- Mating faces of the PSC internal contour machined.

Supplied with:**Torx® clamping wrench.****Optional extras:**

Coolant tube No. 309885; socket No. 309893.

Technical description

Overhang dimension A	93.1 mm
External Ø D	50 mm
Spare Torx® chuck key No. 625220	TX25
Clamping range	1 - 16 mm
Adapter	PSC 63
Arbor standard	ISO 26623-1
Through-coolant	yes
Balance quality G at rotational speed	G 2.5 at 18,000 rpm

Concentricity	$\leq 3 \mu\text{m}$
maximum tightening torque $M_{d \max}$	$\leq 14 \text{ Nm}$
Type of product	Short drill chuck