



Short drill chuck Form A, HSK-A 63, Clamping range: 2,5-16mm



Order data

Order number	307765 2,5-16
GTIN	4045197932006
Item class	32K

Description

Version:

- For clockwise and anticlockwise rotation.
- With RFID/Balluffchip bore.
- Slim design.
- Specific coolant transfer to tools with IC.
- Optimum holding torques at the tool.

Supplied with:

Clamping wrench with T-handle.

Optional extras:

Socket wrench No. 309890. Coolant tube No. 309880.

Technical description

Type	slim
Clamping range	2.5 - 16 mm
Spare Torx® chuck key No. 625220	TX25
External Ø D	50 mm
Overhang dimension A	104 mm
Adapter	HSK-A 63
Shape	A
Balance quality G at rotational speed	G 6.3 at 15,000 rpm

Concentricity	≤ 50 μm
maximum tightening torque $M_{d \max}$	≤ 14 Nm
Type of product	Short drill chuck