



## Electronic torque wrench / rotational angle wrench without plug-in head, maximum torque: 200N·m



### Order data

Order number	655235 200
GTIN	4018754222834
Item class	63A

### Description

#### Version:

Highly precise electronic torque / rotational angle wrench for screw tightening and checking of screw fastenings. Clear OLED display with colour screen and extremely simple menu navigation. Sturdy wrench with "Direct mode" for quick general-purpose use. Up to 200 screw tightening cases can be programmed, which can be incorporated in procedural plans. 4 measurement modes: torque and angle of rotation. Process reliability results achieved by torque with angular monitoring or rotational angle with torque monitoring. Can be programmed by a PC; password protection for security against tampering. Rotary angle measurement can be programmed easily, no reference arm required. Peak and Track function modes.

The wrench can be used in trigger mode. When the set torque or rotational angle is reached the wrench triggers with audible and tactile signals like a conventional mechanical torque wrench.

**Units of measure:** Nm, lbfft, lbfin.

- **Reversible ratchet**
- **Easy input of pitch settings: For tools with a different pitch setting simply input the new pitch. No laborious calculations with formulae.**
- **QuickRelease: Secure engagement and quick change of plug-in heads.**
- **Data output: The USB interface allows the saved data to be read out and analysed via PC.**
- **Easy to use: All functions can be selected using the arrow keys. Clear and simple menu navigation.**
- **Warning signals: – Acoustic (buzzer) – Visual via 3 LEDs and a colour screen**
- **2-component handle: Resistant to oils, greases, fuels, and Skydrol.**

MANOSKOP® 714 electromechanical rotation angle torque wrench combines the best of two worlds. Users benefit from a precise, electronic measurement, but can also feel and hear the well-known "clicking" of mechanical torque wrenches.

#### Standard:

Geprüft nach DIN EN ISO 6789.

#### Cutting dataa:

#### Legend for drawing and formula:

$l_1$  = Lever length without plug-in head  
 $l_2$  = Adjusted reference dimension on the torque wrench  
 $l_3$  = Lever length including factory calibration reference dimension  
 $l_4$  = Reference dimension of the plug-in head  
 L = Total length of the tool  
 $T_1$  = Torque to be set  
 $T_2$  = Specified torque

**Supplied with:**

With sturdy plastic case (size 400 in a sturdy sheet metal case) and 4 batteries (1.5 V micro / AAA / LR3), USB data cable, and SENSOMASTER 4 software for transmitting the measured data.

**Note:**

Suitable Bluetooth module available via eShop (No. 52110220).

## Technical description

Resolution	0.1 Nm
Weight	1360 g
Socket for plug-in head	14×18 mm
maximum torque	200 Nm
Torque measuring accuracy	±2 %
Exchangeable tool	Plug-in head
Torque range	20 - 200 Nm
Torque range	15 - 150 lbfft
Article no of the battery / rechargeable battery fitted	081557 LR3
Number of batteries contained	4
Torque range	180 - 1800 lbfin
Series	MANOSKOP® 714
Adjusted reference dimension on the torque wrench [ $l_2$ ]	25 mm
Connection format	for plug-in heads (rectangular socket)
Lever length including factory calibration reference dimension [ $l_3$ ]	541 mm
Adjustable trigger value	adjustable
Trigger principle	mechanical short-travel release
Overall length L	547 mm

Standard	DIN EN ISO 6789
Lever length without plug-in head [L <sub>1</sub> ]	516 mm
Display	digital
Reversible reading	Nm
Reversible reading	lbf·in
Reversible reading	lbf·ft
Measurement process	Torque
Measurement process	Rotation angle
Feedback	visning
Feedback	udløsning
Setting the trigger value	digital, adjustable
Calibration	O3
Calibration	O5
Calibration	O1
Direction of tightening	For right- and left-hand tightening
Test certificate	Manufacturer's test certificate
Interface	USB interface
Measuring accuracy rotational angle	±1 %
Data can be recorded	yes
Measurement technology	electronic
Release signalling	optisk
Release signalling	akustisk
Release signalling	haptisk
Power supply	Battery-powered
Type of product	Torque Wrench

## Services

DAkkS calibration Torque wrench maximum torque 1000 N·m

020020 1000

020010 400

CalibrationTorque wrench maximum torque 400 N·m

## Accessories

Plug-in ratchet reversible Type-Square drive 2-3/4 in	657600 2-3/4
Plug-in ratchet reversible Type-Square drive 2-1/2 in	657600 2-1/2
Alkaline-manganese batteries International size LR3	081561 LR3
Alkaline-manganese batteries International size LR3	081551 LR3
Plug-in ratchet reversiblewith QuickRelease ejector Type-Square drive 2-1/2 in	657590 2-1/2
Plug-in ratchet reversible Type-Square drive 2-3/4HD in	657600 2-3/4HD