


**HSS jobber drill N, TiN, Ø DC h8: 10mm****Order data**

Order number	GG1365 10
GTIN	4045197910950
Item class	GGN

**Description****Version:**

With point geometry shape C from size 2.4 mm.

Standard core without core taper.

Precision ground point.

**Profile ground:**

High concentricity and pitch accuracy.

Drills for series production use.

**Same as No. 114360.**

**Recommendation:****Maximum drilling depth:**

$$L_2 = L_c - 1.5 \times D_c$$

**Technical description**

Shank Ø D <sub>s</sub>	10 mm
Standard	DIN 338
Feed f in steel < 500 N/mm <sup>2</sup>	0.16 mm/rev.
Flute length L <sub>c</sub>	87 mm
Number of cutting edges Z	2
Nominal Ø D <sub>c</sub>	10 mm

Tolerance nominal $\varnothing$	h8
Overall length L	133 mm
Point angle	118 degrees
Shank	Plain shank
Contents	20
Coating	TiN
Tool material	HSS
Type	N
Helix angle	35-40 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

## User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	56 m/min	N
Alu > 10% Si	suitable only under restricted conditions	50 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	50 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	37 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	31 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable only under restricted conditions	12 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	10 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	15 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	10 m/min	M

Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions	6 m/min	S
GG(G)	suitable	31 m/min	K
CuZn	suitable only under restricted conditions	80 m/min	N
Oil	suitable		
wet maximum	suitable		

---

## Accessories

Jobber drill HSSN Ø DC h8 10 mm

114360 10