



## Water-tight case "Explorer", Type: 4419



### Order data

Order number	692930 4419
GTIN	8024482015316
Item class	64A

### Description

**Version:**

Extremely sturdy tool case of impact resistant plastic, filled with pre-shaped chequer foam. Lockable with padlock No. 085830 – 085875. Thick walls throughout for high stability. Pressure-tight and resistant to chemicals. Temperature-resistant from –33 °C to 90 °C. Heavenly Delight versions with a weight saving of approx. 30% and increased strength compared to previous models.

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

**Application:**

For protection, packaging, and transport of delicate parts and devices.

**Note:**

Many other case sizes, fittings variants, and accessories available on request.

### Technical description

Internal dimension height	190 mm
External dimension height	212 mm

Internal dimension length	445 mm
maximum loading	25 kg
External dimension width	414 mm
Number of catches	2
External dimension length	485 mm
Weight	2.91 kg
Volume	29.2 l
Internal dimension width	345 mm
IP Index of Protection	IP 67
Characteristics case	impact resistant
Characteristics case	stackable
Characteristics case	suitable for air travel
Type of product	Tool transport system