



Water-tight case "Explorer", Type: 2712



Order data

Order number	692930 2712
GTIN	8024482010779
Item class	64A

Description

Version:

Extremely sturdy tool case of impact resistant plastic, filled with pre-shaped chequer foam. Lockable with padlock No. 085830 – 085875. Thick walls throughout for high stability. Pressure-tight and resistant to chemicals. Temperature-resistant from –33 °C to 90 °C. Heavenly Delight versions with a weight saving of approx. 30% and increased strength compared to previous models.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

For protection, packaging, and transport of delicate parts and devices.

Note:

Many other case sizes, fittings variants, and accessories available on request.

Technical description

maximum loading	15 kg
External dimension height	143 mm

External dimension width	270 mm
External dimension length	316 mm
Internal dimension width	200 mm
Internal dimension length	276 mm
Number of catches	2
Internal dimension height	120 mm
Weight	1.3 kg
Volume	6.6 l
IP Index of Protection	IP 67
Characteristics case	impact resistant
Characteristics case	stackable
Characteristics case	suitable for air travel
Type of product	Tool transport system