



Water-tight case "Explorer", Type: 5326



Order data

Order number	692930 5326
GTIN	8024482177014
Item class	64A

Description

Version:

Extremely sturdy tool case of impact resistant plastic, filled with pre-shaped chequer foam. Lockable with padlock No. 085830 – 085875. Thick walls throughout for high stability. Pressure-tight and resistant to chemicals. Temperature-resistant from –33 °C to 90 °C.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

For protection, packaging, and transport of delicate parts and devices.

Note:

Many other case sizes, fittings variants, and accessories available on request.

Technical description

Volume	53 l
Weight	11.3 kg
External dimension height	292 mm

Internal dimension width	405 mm
External dimension width	475 mm
Internal dimension height	250 mm
Number of wheels	2
Internal dimension length	538 mm
External dimension length	627 mm
maximum loading	37.2 kg
Number of catches	4
Number of side handles	2
IP Index of Protection	IP 67
Characteristics case	impact resistant
Characteristics case	stackable
Characteristics case	suitable for air travel
Type of product	Tool transport system