



Torque wrench with reversible ratchet, maximum torque: 1000N·m



Order data

Order number	656500 1000
GTIN	4000896141067
Item class	630

Description

Version:

Handy and very compact single-arm torque wrench, adjustable by scale and self-triggering. Extremely high repeat accuracy, since high quality materials are used throughout. Wearing parts, such as compression springs, are specially pre-treated and sorted. Reversible ratchet for left-hand and right-hand tightening.

With built-in **reversible ratchet – for left and right hand tightening.**

Units of measure: Nm **2-piece** with release tool in nylon carrying bag.

Function:

The wrench triggers giving a "signal" (clearly audible acoustic tone and noticeable vibration) and afterwards is immediately ready for use again.

Application:

For medium to larger batch productions.

Standard:

Geprüft nach DIN EN ISO 6789.

Accuracy:

Of the displayed value **only for right-hand tightening:** $\pm 3\%$.

Cutting dataa:

Legend for drawing and formula:

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Note:

Calibration is only possible for right-hand tightening.

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Square drive	3/4 in
maximum torque	1000 Nm
Display	analogue
Weight	10400 g
Torque measuring accuracy	±3 %
Direction of tightening	For right and left-hand tightening
Scale graduation, 1 graduation =	5 Nm
Torque range	400 - 1000 Nm
Measurement process	Torque
Trigger principle	mechanical short-travel release
Overall length L	1789 mm
Standard	DIN EN ISO 6789
Adjustable trigger value	adjustable
Feedback	triggering
Setting the trigger value	with adjustment scale
Reversible reading	Nm
Connection format	Push-through square drive (ratchet)
Lever length including factory calibration reference dimension [l ₃]	1682 mm
Calibration	O1
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Measurement technology	mechanical
Release signalling	akustisk
Release signalling	haptisk

Type of product

Torque Wrench

Services

DAkkS calibration Torque wrench maximum torque 1000 N·m

020020 1000

Calibration Torque wrench maximum torque 1000 N·m

020010 1000