



Torque wrench QuickSelect without plug-in head, maximum torque: 50N·m



Order data

Order number	657094 50
GTIN	4018754139514
Item class	63A

Description

Version:

Sturdy compact one-armed torque wrench, adjustable to scale and self-triggering. The accuracy is sustained for many thousands of operations, because high quality material is used for all wearing parts with stressed parts loaded only briefly on each occasion. Body and handle are of sturdy square section. Scales adjustable. **Anti-clockwise tightening by pushing through the drive shank**

Without any plug-in head (basic model); see No. 657582 – 657950 for suitable plug-in heads.

Units of measure: Nm, lbfft.

Advantage:

- **Ergonomically shaped two-component handle, resistant to aggressive liquids such as fuel, Skydrol etc.**
- **The adjustment scale is placed behind a sight glass for protection against dirt and damage.**
- **Quick, precise, and reliable setting: Pull the setting knob, "Twist" to set the desired value and "Press" to save it. Setting knob moves easily since there is no spring pressure to be overcome.**

Function:

If the set value is reached while using the wrench, the wrench triggers giving a "signal" (acoustic and perceptible) and is then immediately ready for use again.

Application:

Since the set torque can be varied, it is ideal for repairs and short series production.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Direction of tightening: For right and left-hand tightening

Torque measuring accuracy: $\pm 3\%$
 Exchangeable tool: Plug-in head
 Test certificate: Manufacturer's test certificate
 Calibration: O1
 Overall length L: 330 mm
 Torque range: 10 - 50 N·m
 Torque range: 7 - 37 lbfft
 Scale graduation, 1 graduation =: 0.25 N·m
 Weight: 831 g
 Adjusted reference dimension on the torque wrench [I₂]: 17.5 mm

Technical description

Weight	831 g
maximum torque	50 N·m
Display	analogue
Socket for plug-in head	9×12 mm
Torque measuring accuracy	$\pm 3\%$
Direction of tightening	For right and left-hand tightening
Exchangeable tool	Plug-in head
Scale graduation, 1 graduation =	0.25 N·m
Torque range	10 - 50 N·m
Torque range	7 - 37 lbfft
Lever length including factory calibration reference dimension [I ₃]	297.5 mm
Reversible reading	Nm
Reversible reading	lbfft
Setting the trigger value	with adjustment scale
Standard	DIN EN ISO 6789
Feedback	triggering
Adjusted reference dimension on the torque wrench [I ₂]	17.5 mm
Lever length without plug-in head [I ₁]	280 mm
Connection format	for plug-in heads (rectangular socket)
Overall length L	330 mm

Measurement process	Torque
Adjustable trigger value	adjustable
Trigger principle	mechanical short-travel release
Calibration	O1
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Measurement technology	mechanical
Release signalling	akustisk
Release signalling	haptisk
Series	MANOSKOP® 730N
Type of product	Torque Wrench

Services

Labelling laser-etched Type	018940
Calibration Torque wrench maximum torque 400 N·m	018820 400
DAkkS calibration Torque wrench maximum torque 1000 N·m	018830 1000
DAkkS calibration Torque wrench maximum torque 1000 N·m	020020 1000
Calibration Torque wrench maximum torque 400 N·m	020010 400

Accessories

Plug-in ratchet reversible Type-Square drive 1-3/8 in	657600 1-3/8
Plug-in ratchet reversible with QuickRelease ejector Type-Square drive 1-1/2 in	657590 1-1/2
Plug-in ratchet reversible with QuickRelease ejector Type-Square drive 1-3/8 in	657590 1-3/8
Square drive plug-in head Type-Square drive 1-1/2 in	657700 1-1/2
Square drive plug-in head Type-Square drive 1-3/8 in	657700 1-3/8
Plug-in ratchet reversible Type-Square drive 1-1/4 in	657600 1-1/4

Plug-in ratchet reversible with QuickRelease ejector Type-Square drive 1-1/4 in	657590 1-1/4
Plug-in ratchet reversible Type-Square drive 1-1/2 in	657600 1-1/2
Square drive plug-in head Type-Square drive 1-1/4 in	657700 1-1/4