

**Torque sensor for TTS-2000, maximum torque: 1355N·m****Order data**

Order number	654910 1355
GTIN	856986007065
Item class	66D

**Description****Version:**

The built-in SMART chip stores the sensor identification, so that all system components are interchangeable. The torque sensor can withstand a mechanical overload up to 150% of the nominal value. On reaching of 110% of nominal value the sensor emits an acoustic warning signal, plus in addition a visual warning appears on the display. The torque sensor is equipped with a durable cable proof against polarity inversion, which can be exchanged if necessary without problems.

**Standard:**

Vierkantantriebe nach DIN 3120 / ISO1174-1.

**Technical description**

Cable length	1.2 m
Weight	3.2 kg
Torque measuring accuracy	±1 %
Diameter	64 mm

Torque range	135 - 1355 Nm
Length	178 mm
maximum torque	1355 Nm
Drive square	1 in
Square drive	1 in
Direction of tightening	For right and left-hand tightening
Test certificate	Manufacturer's test certificate
Type of product	Torque testing device