

**Garant**
**Solid carbide copy slot drill, Diamond, Ø DC × L1: 1,2X15mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 209791 1,2X15 |
| GTIN         | 4045197920096 |
| Item class   | 11Y           |

**Description**
**Version:**

With **crystalline diamond sp<sup>3</sup> coating**. For the **highest demands regarding performance and precision** in fibre-reinforced composites, CRP, GRP, and graphite. **Extremely tight tolerances** ensure maximum accuracy. Double relief ground with 2 hollow-ground chamfers. **Recess angle  $\alpha = 16^\circ$** .

Tolerances:

- **Corner radius: Radius contour 0 / -0.005 mm.**
- **Neck Ø:  $D_1 = 0 / -0.01$  mm.**

**Note:**

At greater tool overhang lengths, use a reduced value for  $a_p$ !  
values for:

copying:  $a_p = 0.15 \times D \times a_{p, \text{korr}}$

**To calculate the feed rate  $v_f$  please use the actual speed of the machine (the maximum possible speed)!**

e.g:  $v_f = 18000 \text{ [rpm]} \times f_z \text{ [mm/Z]} \times z$

**Technical description**

|   |          |
|---|----------|
| Shank Ø $D_s$                           | 4 mm     |
| Overall length L                        | 50 mm    |
| Cutting edge Ø $D_c$                    | 1.2 mm   |
| Overhang length $L_1$ incl. recess      | 15 mm    |
| Feed $f_z$ for copy milling in graphite | 0.025 mm |
| No. of teeth Z                          | 2        |

|   |                                  |
|---|----------------------------------|
| Flute length $L_c$                        | 0.96 mm                          |
| Recess $\varnothing D_1$                  | 1.16 mm                          |
| Corner radius $R_1$                       | 0.6 mm                           |
| Helix angle                               | 30 degrees                       |
| Correction factor $a_{p\text{corr}}$      | 0.35                             |
| Coating                                   | Diamond                          |
| Tool material                             | Solid carbide                    |
| Standard                                  | Manufacturer's standard          |
| Tolerance nominal $\varnothing$           | 0 / -0.005                       |
| Direction of infeed                       | horizontal, oblique and vertical |
| Cutting width $a_e$ for milling operation | 0.05×D for copy milling          |
| Shank                                     | DIN 6535 HA to h5                |
| Through-coolant                           | no                               |
| Colour ring                               | black                            |
| Type of product                           | Ball-nosed slot drill            |

## User data

|                    | Suitability | $V_c$     | ISO code |
|--------------------|-------------|-----------|----------|
| PVDF GF20          | suitable    | 200 m/min | N        |
| POM GF25           | suitable    | 190 m/min | N        |
| PA 66 GF30         | suitable    | 170 m/min | N        |
| PEEK GF30          | suitable    | 150 m/min | N        |
| PTFE CF25          | suitable    | 180 m/min | N        |
| PEEK CF30          | suitable    | 160 m/min | N        |
| Hybrids            | suitable    |           |          |
| Honeycomb sandwich | suitable    | 350 m/min | N        |
| GRP                | suitable    | 190 m/min | N        |
| GRP, CRP           | suitable    | 190 m/min | N        |
| Graphite           | suitable    | 340 m/min | N        |

|             |          |
|-------------|----------|
| wet minimum | suitable |
| dry         | suitable |
| Air         | suitable |