



Enclosed trolley with 5 platforms, Type: 5392



Order data

Order number	919882 5392
GTIN	4017976013176
Item class	96F

Description

Version:

Steel angle section construction with tubular pushing handle. End walls, 1 side wall and roof clad with 40×40×4 mm wire mesh, fully welded. Positive bar locking with pivoting handle and padlock. 1 fixed platform and 4 loose shelves of chipboard with beech grain surface. Intermediate shelves adjustable at 100 mm intervals. The bottom shelf is not adjustable. 2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings. TOTALSTOP central braking system on the castors.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Height adjustment interval: 100

Height: 1792 mm

Width: 1170 mm

Depth: 745 mm

Platform area width: 1000 mm

Platform area depth: 680 mm

Height of shelf 1: 292 mm

Technical description

Standard	EN 1757-3
Height of shelf 5	1482 mm
Push handle	yes
Height	1792 mm
Number of fixed wheels without parking brake	2
Weight	144 kg
Load capacity of each loose shelf	90 kg
Width	1170 mm
Type	5392
Platform area width	1000 mm
Height of shelf 1	292 mm
Number of castors with parking brake	2
Material of wheel	TPE
Material of loose shelf	Sandwich boards with beech-effect surface.
Wheel Ø	200 mm
Height of shelf 4	1182 mm
Total load capacity	750 kg
Height of shelf 2	582 mm
Height of shelf 3	882 mm
Depth	745 mm
Platform area depth	680 mm
Height adjustment interval	100
Type of product	Enclosed trolley