

**Enclosed trolley, Type: 1550****Order data**

Order number	919877 1550
GTIN	4017976015507
Item class	96F

Description**Version:**

Enclosed trolley with one **removable** longitudinal side. Platform made of chipboard with beech grain surface finish, welded steel construction, 2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Type	1550
Number of fixed wheels without parking brake	2
Platform area height	228 mm
Material of wheel	TPE
Wheel Ø	160 mm

maximum load capacity	500 kg
Weight	35 kg
Height	948 mm
Width	1030 mm
Number of castors with parking brake	2
Platform area width	850 mm
Platform area depth	500 mm
Depth	509 mm
Type of product	Enclosed trolley