

HOLEX®**Torque wrench with ratchet and adjustment scale, maximum torque: 200 N·m****Order data**

Order number	657270 200
GTIN	4045197368638
Item class	62E

Description**Version:**

Robust torque wrench, adjustable with micrometer scale, with protection against accidental changes to the setting.

Integral ratchet to accept sockets. Ratchet with captive **push-through square drive pin** for **right-hand and left-hand tightening**.

Function:

On reaching the set torque value the wrench triggers giving a "signal" (audible and perceptible) and is then immediately ready for use again.

Application:

For controlled tightening of screws to pre-set torque. For small to medium series.

Standard:

Geprüft nach DIN EN ISO 6789.

Accuracy:

±4 % of the displayed value.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Direction of tightening: For right and left-hand tightening

Torque measuring accuracy: ±3 %

Test certificate: Manufacturer's test certificate

Calibration: O1

Overall length L: 495 mm

Torque range: 40 - 200 N·m

Scale graduation, 1 graduation =: 1 N·m

Weight: 1200 g

Square drive: 1/2 inch

Technical description

Deflection function	
Memory pointer	
Packaging	
Quick release/ quick-change function	
electrical insulation	
Slipper function	
Type of product	