



Enclosed trolley, Type: 1551



Order data

Order number	919877 1551
GTIN	4017976015514
Item class	96F

Description

Version:

Enclosed trolley with one **removable** longitudinal side. Platform made of chipboard with beech grain surface finish, welded steel construction, 2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Type	1551
Width	1180 mm
Number of fixed wheels without parking brake	2
Weight	40 kg
Platform area width	1000 mm

Height	990 mm
maximum load capacity	600 kg
Platform area height	270 mm
Wheel Ø	200 mm
Material of wheel	TPE
Number of castors with parking brake	2
Platform area depth	600 mm
Depth	609 mm
Type of product	Enclosed trolley