

**Alligator® water pump pliers VDE grips, overall length: 250mm****Order data**

Order number	705740 250
GTIN	4003773039303
Item class	73F

**Description****Version:**

**Box joint** (= double guidance). Designed to prevent fingers being trapped. Induction hardened. Notched serrated jaws, self-clamping on pipes and nuts. Multi-position stepped adjustment.

**Insulated to DIN EN IEC 60900 / VDE 0682-201** for working at voltages up to 1000 V.

Pliers chrome-plated, handles insulated with multi-component covering.

**Standard:**

**DIN ISO 8976**

**Material:**

Chrome vanadium steel, drop forged.

**Technical description**

overall length	250 mm
Jaw capacity for pipes	2 in
Hexagon across flats	46 mm
Handle	Multi-component covering
Manufacturer's designation	Alligator
Surface	chrome-plated
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 8976
Material	Chrome vanadium steel

non-sparking	no
Stepped fine adjustment	no
Self-locking	yes
Protection against trapping fingers	yes
Type of product	Pipe wrench and water pump pliers