



Table trolley with 2 platforms, Type: 2401B



Order data

Order number	919868 2401B
GTIN	4017976524016
Item class	96F

Description

Version:

Welded steel construction,
2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings.
Steel plate platforms **flush** with the frame.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Platform area depth	600 mm
Number of fixed wheels without parking brake	2
Height of top shelf	900 mm
Material of wheel	TPE
Platform area width	1000 mm

Depth	609 mm
Load capacity of top shelf	200 kg
maximum load capacity	600 kg
Height	900 mm
Standard	EN 1757-3
Width	1197 mm
Type	2401B
Number of castors with parking brake	2
Height of bottom shelf	270 mm
Weight	56 kg
Wheel Ø	200 mm
Type of product	Table trolleys