

Garant**Circular saw blade, TiAlN, Ø×thickness: 125X2mm****Order data**

Order number	179915 125X2
GTIN	4045197938091
Item class	17C

Description**Version:**

GARANT solid carbide circular saw blade with extra narrow cutting width in order to minimise the loss of material. The cutting speed can be **increased by a factor of 3 to 4** compared to HSS saw blades. Reinforced collar for a significant increase in the stability of the saw blade. For flat base of the slot.

Note:

The tolerances for the circular saw blade diameter are considerably better than the values permissible to DIN 1837/1838, in some cases by up to 50%. Tooth profile BW.

Technical description

Ø	125 mm
Bore Ø	22 mm
Collar thickness E	2.4 mm
Thickness	2 mm
Hub Ø	50 mm

Feed f_z in steel < 900 N/mm ²	0.025 mm
maximum cutting depth $a_{e,max}$	36 mm
No. of teeth Z	50
suitable adapter	179902 160
Number of drive holes	5
Drive hole \varnothing	4.4 mm
Drive hole pitch circle	43.5 mm
Coating	TiAlN
Tool material	Solid carbide
Through-coolant	no
Type of product	Circular saw blade

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	800 m/min	N
Alu > 10% Si	suitable only under restricted conditions	400 m/min	N
Steel < 500 N/mm ²	suitable	180 m/min	P
Steel < 750 N/mm ²	suitable	130 m/min	P
Steel < 900 N/mm ²	suitable	120 m/min	P
Steel < 1100 N/mm ²	suitable	85 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	35 m/min	P
INOX < 900 N/mm ²	suitable	90 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	70 m/min	M
CuZn	suitable only under restricted conditions	200 m/min	N
Uni	suitable only under restricted conditions		

wet maximum	suitable
Air	suitable only under restricted conditions