

Garant**Torque wrench "Slipper" without scale, maximum torque: 3N·m****Order data**

| | |
|--------------|---------------|
| Order number | 657765 3 |
| GTIN | 4045197609007 |
| Item class | 61E |

Description**Version:**

The special slipping trigger mechanism **reliably prevents unintentional overtightening**. Torque wrench **without scale**. Wrench setting using torque analyser. **With friction ratchet**, working angle = 0°.

Handy and lightweight aluminium handle, ideal for applying small torques.

Advantage:

Precision triggering mechanism facilitates working in inaccessible places.

Function:

On reaching the set torque value the wrench triggers a clearly detectable deflection and is then immediately ready for use again. The special trigger mechanism ensures that the set torque values are reliably achieved, **but not exceeded**.

Application:

For medium to larger batch productions.

Standard:

Geprüft nach DIN EN ISO 6789.

Accuracy:

±4 % of the set value.

Cutting dataa:**Legend for drawing and formula:**

l_1 = Lever length without plug-in head
 l_2 = Adjusted reference dimension on the torque wrench
 l_3 = Lever length including factory calibration reference dimension
 l_4 = Reference dimension of the plug-in head
 L = Total length of the tool
 T_1 = Torque to be set
 T_2 = Specified torque

Technical description

| | |
|---------------------------|---|
| maximum torque | 3 Nm |
| Weight | 130 g |
| Square drive | 1/4 in |
| Torque measuring accuracy | ±4 % |
| Direction of tightening | Right-hand tightening |
| Torque range | 0.3 - 3 Nm |
| Feedback | triggering |
| Measurement process | Torque |
| Setting the trigger value | without setting scale (requires torque analyser) |
| Standard | DIN EN ISO 6789 |
| Reversible reading | Nm |
| Trigger principle | mechanical slip clutch |
| Connection format | Push-through square drive (ratchet) |
| Adjustable trigger value | preset |
| Overall length L | 124 mm |
| Calibration | O6 |
| Calibration | O7 |
| Test certificate | Manufacturer's test certificate |
| Data can be recorded | no |
| Measurement technology | mechanical |
| Release signalling | akustisk |
| Release signalling | haptisk |

| | |
|-----------------|---------------|
| Type of product | Torque Wrench |
|-----------------|---------------|

Services

| | |
|---|-------------|
| AdjustmentTorque wrench without scale Type SET | 020080 SET |
| Calibration and adjustmentTorque wrench without scale maximum torque 400 N·m | 020090 400 |
| DAkkS calibration and adjustmentTorque wrench without scale maximum torque 1000 N·m | 020190 1000 |

Accessories

| | |
|---|-----------|
| Electronic torque analyser“ProTest” maximum torque 60 N·m | 654460 60 |
| Torque analyser for torque wrenches“SmartCheck” maximum torque 10 N·m | 654650 10 |