



HSS jobber drill N, uncoated, Ø DC h8: 26,5mm



Order data

Order number	116320 26,5
GTIN	4045197029775
Item class	12C

Description

Version:

Special surface treatment, resulting in reduced tendency to edge build-up **and improved chip evacuation.**

Recommendation:

Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c.$$

Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530.**

Technical description

Feed f in steel < 750 N/mm ²	0.25 mm/rev.
Number of cutting edges Z	2
Nominal Ø D _c	26.5 mm
Flute length L _c	165 mm
Tolerance nominal Ø	h8
Overall length L	286 mm
Morse taper MT size	3
Standard	DIN 345
recommended maximum drilling depth L ₂	125.3 mm
Point angle	118 degrees
Shank	Morse taper

Coating	uncoated
Tool material	HSS
Type	N
Helix angle	20-30 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable	40 m/min	P
Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	25 m/min	P
GG(G)	suitable only under restricted conditions	25 m/min	K
Oil	suitable		
wet maximum	suitable		