

Garant
Adjustable spanner plug-in head, Type-Opening width: 2-41 mm

Order data

Order number	657850 2-41
GTIN	4045197596161
Item class	61E

Description
Version:

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

Great versatility due to the adjustable opening width.

Caution:

Reference dimension correction necessary on the torque wrench (change to the setting value).

Advantage:

Adjustment of the opening width **does not necessitate modification of the reference dimension.**

Material:

Chrome vanadium steel, chrome-plated.

Cutting dataa:
Legend for drawing and formula:

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Suitable for:

Torque wrench with rectangular sockets.

Note:

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

Technical description

Width b	88.6 mm
Plug-in shank	14×18 mm
Height h	20.4 mm
Opening width	1/4 – 1.1/2 in
Opening width	7 - 41 mm
Pitch S	85.4 mm
Exchangeable tool	Plug-in head
Type of product	Open ended plug-in head