



## Alligator® water pump pliers VDE dip insulated, overall length: 250mm



### Order data

Order number	705730 250
GTIN	4003773019343
Item class	73F

### Description

#### Version:

**Box joint** (= double guidance). Designed to prevent fingers being trapped. Induction hardened. Notched serrated jaws, self-clamping on pipes and nuts. Multi-position stepped adjustment.

**Insulated to DIN EN IEC 60900 / VDE 0682-201** for working at voltages up to 1000 V.

Jaws chrome plated, handles dip insulated.

#### Standard:

**DIN ISO 8976**

#### Material:

Chrome vanadium steel, drop forged.

### Technical description

overall length	250 mm
Jaw capacity for pipes	2 in
Hexagon across flats	46 mm
Handle	dip insulated
Manufacturer's designation	Alligator
Surface	chrome-plated
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 8976
Material	Chrome vanadium steel

non-sparking	no
Stepped fine adjustment	no
Self-locking	yes
Protection against trapping fingers	yes
Type of product	Pipe wrench and water pump pliers