

**Garant**
**Tap wrench, adjustable strengthened, Type: 0**

**Order data**

Order number	148200 0
GTIN	4045197923929
Item class	11K

**Description**
**Version:**

With hardened jaws and steel grips. For use in confined spaces one steel handle can be unscrewed.

For **heavy** duties and **precision applications**. All dimensions with **high-quality forged steel base bodies** and integral fixed jaws. **Round vials** for straight application.

Standard: DIN 1814

Capacity □: 2 - 5 mm

for hand taps DIN 352: M1 – M8

for hand reamer Ø DIN 206: 2.5 - 6.5 mm

Overall length: 125 mm

**Technical description**

for hand taps DIN 352	M1 – M8
Capacity □	2 - 5 mm
Overall length	125 mm
for hand reamer Ø DIN 206	2.5 - 6.5 mm
Standard	DIN 1814
Type of product	Tap wrench