

Garant
Tap wrench, adjustable strengthened, Type: 2

Order data

Order number	148200 2
GTIN	4045197923950
Item class	11K

Description
Version:

With hardened jaws and steel grips. For use in confined spaces one steel handle can be unscrewed.

For **heavy** duties and **precision applications**. All dimensions with **high-quality forged steel base bodies** and integral fixed jaws. **Round vials** for straight application.

Standard: DIN 1814

Capacity □: 3 - 9 mm

for hand taps DIN 352: M4 – M12

for hand reamer Ø DIN 206: 5 - 10 mm

Overall length: 265 mm

Technical description

Capacity □	3 - 9 mm
Overall length	265 mm
for hand taps DIN 352	M4 – M12
for hand reamer Ø DIN 206	5 - 10 mm
Standard	DIN 1814
Type of product	Tap wrench