

Garant
Tap wrench, adjustable strengthened, Type: 5

Order data

| | |
|--------------|---------------|
| Order number | 148200 5 |
| GTIN | 4045197923981 |
| Item class | 11K |

Description
Version:

With hardened jaws and steel grips. For use in confined spaces one steel handle can be unscrewed.

For **heavy** duties and **precision applications**. All dimensions with **high-quality forged steel base bodies** and integral fixed jaws. **Round vials** for straight application.

Standard: DIN 1814

Capacity □: 7 - 20 mm

for hand taps DIN 352: M12 – M33

for hand reamer Ø DIN 206: 9 - 26 mm

Overall length: 700 mm

Technical description

| | |
|---------------------------|------------|
| for hand reamer Ø DIN 206 | 9 - 26 mm |
| Capacity □ | 7 - 20 mm |
| for hand taps DIN 352 | M12 – M33 |
| Overall length | 700 mm |
| Standard | DIN 1814 |
| Type of product | Tap wrench |