

Garant
Tap wrench, adjustable strengthened, Type: 3

Order data

Order number	148200 3
GTIN	4045197923967
Item class	11K

Description
Version:

With hardened jaws and steel grips. For use in confined spaces one steel handle can be unscrewed.

For **heavy** duties and **precision applications**. All dimensions with **high-quality forged steel base bodies** and integral fixed jaws. **Round vials** for straight application.

Standard: DIN 1814

Capacity □: 4.9 - 12 mm

for hand taps DIN 352: M5 – M20

for hand reamer Ø DIN 206: 6.5 - 15 mm

Overall length: 370 mm

Technical description

for hand reamer Ø DIN 206	6.5 - 15 mm
Capacity □	4.9 - 12 mm
for hand taps DIN 352	M5 – M20
Overall length	370 mm
Standard	DIN 1814
Type of product	Tap wrench