

**Garant****Tap wrench, adjustable strengthened, Type: 7****Order data**

Order number	148200 7
GTIN	4045197924209
Item class	11K

**Description****Version:**

With hardened jaws and steel grips. For use in confined spaces one steel handle can be unscrewed.

For **heavy** duties and **precision applications**. All dimensions with **high-quality forged steel base bodies** and integral fixed jaws. **Round vials** for straight application.

**Technical description**

for hand reamer Ø DIN 206	20 - 45 mm
for hand taps DIN 352	M25 – M58
Overall length	1258 mm
Capacity □	14.5 - 36 mm
Standard	DIN 1814
Type of product	Tap wrench