



## Cordless hammer drill, Type: GBH18VEC



### Order data

|              |                 |
|--------------|-----------------|
| Order number | P07551 GBH18VEC |
| GTIN         | 3165140924016   |
| Item class   | 03B             |

### Description

#### Version:

- Long operating time (> 190 holes 6 × 40 mm in concrete) on a single battery charge (5.0 Ah) thanks to the efficient Bosch EC motor.
- Low weight (only 2.7 kg) and compact design for more comfortable working.
- Innovative CoolPack batteries ensure optimum dissipation of heat, thereby extending the working life by up to 100 % (compared to Li-ion batteries without Cool-Pack).

#### Supplied with:

3 × Li-ion battery 18 V/ 5.0 Ah, charger GAL 1880CV, L-BOXX, USB adapter.

### Technical description

|  |                       |
|--|-----------------------|
| Tool arbor shape                                     | SDS-Plus              |
| Impact energy  | 1.7 J                 |
| Packaging  | Modular case (L-Boxx) |
| suitable battery - supplier / battery type / voltage | Bosch 18 V            |
| Manufacturer's designation                           | GBH 18VEC             |
| Battery capacity                                     | 5 Ah                  |
| Battery voltage                                      | 18 V                  |

|  |                              |
|--|------------------------------|
| Number of rechargeable batteries contained | 3                            |
| Power supply                               | Rechargeable battery-powered |
| Type of product                            | Hammer drill                 |