



## Weld-on plug-in head, Type: 2



### Order data

Order number	657950 2
GTIN	4018754034604
Item class	63A

### Description

**Version:**

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

**Application:**

To take customer's own tools, e.g. a special crank wrench. The scale has to be corrected in accordance with the length of the part welded on.

**Cutting dataa:****Legend for drawing and formula:**

$l_1$  = Lever length without plug-in head

$l_2$  = Adjusted reference dimension on the torque wrench

$l_3$  = Lever length including factory calibration reference dimension

$l_4$  = Reference dimension of the plug-in head

$L$  = Total length of the tool

$T_1$  = Torque to be set

$T_2$  = Specified torque

**Suitable for:**

Torque wrench with rectangular sockets.

### Technical description

Length l	12 mm
Height h	11 mm
Plug-in shank	14×18 mm
Plug-in head (tool blank)	11×25 mm
Series	737/40
Pitch S	12 mm
Exchangeable tool	Plug-in head
Type of product	Weld-on plug-in head (tool-blank)