

Garant

GARANT Power Q high feed rate indexable milling cutter, Weldon shank, \varnothing D / number of effective cutting edges Z: 30/2mm


Order data

Order number	212813 30/2
GTIN	4045197939227
Item class	210

Description
Spare part:

Pack of insert screws No. 219812 (15IP; 5.0Nm).

Note:

Use GARANT torque screwdriver TQ No. **211750 size 5.0** with bit No. **674252 size 15IP**.

Technical description

Cutting edge $\varnothing D_c$	30 mm
Overhang L_1	40 mm
Shank $\varnothing D_s$ h6	32 mm
suitable indexable insert	XDM.120516
Circular interpolation milling $\varnothing D_{min}$	44 mm
Circular interpolation milling a_p	1.5 mm
Number of cutting edges Z	2
Through-coolant	yes
Ramping length L for α_{max}	10.34 mm
Ramping angle α_{max}	4.42 degrees
Overall length L_{tot}	100 mm
Circular interpolation milling $\varnothing D_{max}$	58 mm

Ø D ₃	14 mm
Series	Power Q
Setting angle κ	11 degrees
Shank type	Weldon shank
Milling application	Plunging
Milling application	Ramping
Milling application	Circular milling
Machining strategy	HPC
Tool exchange	PowerCard
Type of product	Copy mill

Accessories

Torque screwdriver, fixed setting set torque 5,0 N·m	211750 5,0
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP