



BIT ratchet socket plug-in head, Bit-holder: 5/16in



Order data

Order number	657940 5/16
GTIN	4018754154715
Item class	63A

Description

Version:

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

Ratchet reversible for clockwise / anticlockwise tightening.

Application:

To take bits with hexagon shank to DIN ISO 1173 C 8 and E 8 (5/16 inch).

Material:

Chrome alloy steel, non-flaking, chrome-plated over nickel.

Cutting dataa:

Legend for drawing and formula:

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Suitable for:

Torque wrench with rectangular sockets.

Note:

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

The rated load on this plug-in head is limited to the corresponding jaw width, and may be less than that of the torque wrench.

Technical description

Height h	17.9 mm
Plug-in shank	9×12 mm
Width b	29 mm
Long-term rated loading	40 Nm
Bit-holder	5/16 in
Exchangeable tool	Plug-in head
No. of teeth	30
Series	725B
Pitch S	28 mm
Material	Chrome alloy steel
Ratchet reversible	yes
Tool with ratchet function	yes
Type of product	BIT ratchet socket plug-in head