

**Electronic torque screwdriver, maximum torque: 200cNm****Order data**

Order number	659050 200
GTIN	4045197503879
Item class	62E

Description**Version:**

Torque screwdriver with a flexible range of applications; with a 2-component handle, large display and quick-change coupling shank for bits. When the set value is reached, the torque screwdriver gives a clear visual and audible signal. 2 working modes are available - peak value display and tracking value display. Stores up to 50 values.

Units of measure: cNm, lbf·in, kgf·cm

Application:

Torque control; controlled tightening of screws in a single operation or for small batch production.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Resolution	0.1 cNm
Weight	200 g
maximum torque	200 cNm
Torque measuring accuracy	±2 %
Torque range	40 - 200 cNm
Number of batteries contained	1
Release signalling	optisk

Release signalling	akustisk
Reversible reading	cNm
Reversible reading	lbf·in
Display	digital
Setting the trigger value	digital, adjustable
Measurement process	Torque
Connection format	Bit holder 1/4 inch
Overall length L	203 mm
Trigger principle	Electromechanical trigger
Feedback	displaying
Adjustable trigger value	adjustable
Calibration	O3
Direction of tightening	For right- and left-hand tightening
Test certificate	Manufacturer's test certificate
Bit socket	F 6.3
Standard	DIN EN ISO 6789
Data can be recorded	yes
Measurement technology	electronic
Battery type	LR3
Power supply	Battery-powered
Type of product	Torque screwdriver

Services

CalibrationTorque screwdrivers, clockwise / anti-clockwise maximum torque 0,04-20/2 N·m	020260 0,04-20/2
---	------------------

Accessories

Battery compartment cover Type 1	655346 1
Alkaline-manganese batteries International size LR3	081551 LR3

Coin-Driver Blade length 45 mm	664310 45
Coin-Driver, short Blade length 45 mm	664311 45
Alkaline-manganese batteries International size LR3	081561 LR3