

**KANON**
**Minimal torque gauge, maximum torque: 90cNm**

**Order data**

Order number	658800 90
GTIN	4582126965464
Item class	66F

**Description**
**Version:**

Accurate measuring instrument for the smallest torques. Easy-to-read scale with memory pointer on the top and additional scale on the side. **With 3-jaw steel chuck.**

**Application:**

For measuring the smallest torques (such as rotation and frictional resistances) and for controlled tightening of screws.

**Standard:**

Geprüft nach DIN EN ISO 6789.

**Note:**

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

**Technical description**

Ø	63 mm
Clamping chuck range	1 - 8.5 mm
Weight	600 g
maximum torque	90 cNm
Torque range	10 - 90 cNm
Torque range	100 - 900 mNm
Setting the trigger value	Memory pointer
Feedback	displaying

Scale graduation, 1 graduation =	2 cNm
Overall length L	132 mm
Release signalling	visual
Adjustable trigger value	non-adjustable
Connection format	3-jaw chuck
Series	SGK
Measurement process	Torque
Standard	DIN EN ISO 6789
Display	analogue
Reversible reading	Nm
Calibration	O3
Direction of tightening	For right- and left-hand tightening
Test certificate	Manufacturer's test certificate
Torque measuring accuracy	±3 %
Data can be recorded	no
Measurement technology	mechanical
Type of product	Torque Wrench

## Services

CalibrationTorque wrench clockwise / anti-clockwise  
maximum torque 400/2 N·m

020030 400/2